sames Sintec

Equipment

REX2B0079-MO-MA-FO-SE	Motor (MO)	Material (MA)	Foot (FO)	Sealing (SE)	Model
Motor choices (Pressure ratio)					WO=5
- Motor 1000 (11:1)	10				MO=10
- Motor 1500 (23:1)	15				MO=15
- Motor 3000 (46:1)	30				MO=30
Lower Material selection					WA=5
- Stainless Steel		SS			MA=SS
Foot selection					FO=?
- Wall mounted (Inlet F 1" BSPP)			WM		FO=WM
- Follower plate (Ø=80mm)			FP		FO=FP
Seal package selection					SE=\$
- PTFE - Polytetrafluorothylene (Teflon like properties)				01	SE=01
- PTFE + FEP (Encapsulated O-Ring: Teflon like properties over Viton or Silicone)				02	SE=02
- PE - Polyethene (UHMWPE)				03	SE=03
- Leather				04	SE=04
- PTFEG (PTFE + Graphite compound)				05	SE=05
- PU (Polyurethane)				06	SE=06



2 Ball Pump

High Viscosity / Pumps

Accessories

Description	Part number
Flat Seal Follower Plate for 20-30L Drums - Ø 280-285 (pump foot Ø80)	151100100
Flat Seal Follower Plate for 30L Drums -Ø 305 (pump foot Ø80)	151100200
Flat Seal Follower Plate for 30L Drums -Ø 315 (pump foot Ø80)	151100300
Flat Seal Follower Plate for 40-60L Drums -Ø 350-360 (pump foot Ø80)	151100400
Flat Seal Follower Plate for 200L Drums -Ø 571 (pump foot Ø80)	151100500
Flat Double Seal Follower Plate for 200L Drums -Ø 571 (pump foot Ø80)	1055180301
Double O-Ring Follower Plate for 20L drum -Ø 280 (pump foot Ø80)	151101100
Double O-Ring Follower Plate for 30L drum -Ø 285 (pump foot Ø80)	151101200
Double O-Ring Follower Plate for 30L drum -Ø 305 (pump foot Ø80)	151101300
Double O-Ring Follower Plate for 30L drum -Ø 315 (pump foot Ø80)	151101400
Double O-Ring Follower Plate for 40-60L drum -Ø 360 (pump foot Ø80)	151101500
Double O-Ring Follower Plate for 200L drum -Ø 571 (pump foot Ø80)	151101600
Double O-Ring PTFE-Coated Follower Plate for 20L drum -Ø 280 (pump foot Ø80)	151102100
Double O-Ring PTFE-Coated Follower Plate for 30L drum -Ø 285 (pump foot Ø80)	151102200
Double O-Ring PTFE-Coated Follower Plate for 30L drum -Ø 305 (pump foot Ø80)	151102300
Double O-Ring PTFE-Coated Follower Plate for 30L drum -Ø 315 (pump foot Ø80)	151102400
Double O-Ring PTFE-Coated Follower Plate for 40-60L drum -Ø 360 (pump foot Ø80)	151102500
Double O-Ring PTFE-Coated Follower Plate for 200L drum -Ø 571 (pump foot Ø80)	151102600
Wall mounted support for motor 1000 to 3000	210008
Monocolumm elevator for 20 to 60 L. drums (not available in NA/China)	151080000
Monocolumm elevator for 200 L. drums (not available in NA/China)	151090000
Double columm elevator for 20 to 60 L. drums (not available in NA/China)	151080500
Double columm elevator for 200 L. drums (not available in NA/China)	151090500



13 chemin de Malacher - CS 70086 38243 Meylan Cedex - FRANCE Phone: +33 (0)4 76 41 60 60 - Fax: +33 (0)4 76 41 60 90 www.sames.com

PUMPING BEYOND POSSIBLE.









REXSON 2B0079

2 Ball Pump

This High Viscosity Pump is a 2 ball double-acting piston technology is used for Airless and extrusion application requiring low flow rates.

sames **S**intec





Switch Motor

The **REXSON pumps of the high viscosity range** have been designed with robustness in mind, and the aim of offering a high degree of modularity to follow your application. Unlike liquid fluid pumping, the high viscosity range imposes highly variable mechanical stresses from one product to another. Double-acting ball pumps are similar in construction to pumps for liquid products and are capable of transferring fluid up to 50,000 Cps. These pumps have been adapted for high viscosity products by optimizing the passage diameters, the nature of the seals, and the hardness of the materials.

To create your own pump that will **meet your application specifications**, you will have to **select**:

- The correct air motor according to the maximum pressure,
- The construction materials according to the nature of the product,
- The foot and mounting style according to the product packaging, and your installation
- The Seal pack (see the Documents tab to get all necessary information on our website).

Our air motors are designed for maximum airflow with a pilot distributor to allow fast inversion. They are equipped with a broad silencer to **avoid water freezing** at the motor outlet and can be controlled (start/stop) from a remote air control. These pumps are used as feeding equipment directly from the product packaging in-wall mounting, or installed on an elevator with a follower plate for open drums.



Technical data table

Designation	Value	Unit: metric (US)		
Maximum Fluid Pressure	320 (4,600)	bar (psi)		
Maximum Air Pressure	6 (87)	bar (psi)		
Viscosity	<50,000	cps		
Pressure Ratio (depending on air motor size)	11:1, 23:1, 46:1	11:1, 23:1, 46:1		
Maximum Temperature	80 (176)	°C (°F)		
Fluid Volume per Cycle	79	сс		
Fluid Output at 15 cycles / mn	1,18 (0.31)	l/mn (gal/mn)		
Fluid Output at 60 cycles / mn	4,74 (1.25)	l/mn (gal/mn)		
Motor Type	1000, 1500, 3000	1000, 1500, 3000		
Air Inlet	1/2"- 3/4"BSP(F)	1/2"- 3/4"BSP(F)		
Fluid Outlet	3/4"BSPP(F)	3/4"BSPP(F)		
Weight (fluid section only)	8 (17.6)	kg (lbs)		
Weight (air motor only)	5,5-7,2 (12.1-15.9)	kg (lbs)		
Fluid Inlet (follower plate)	80mm	80mm		
Fluid Inlet (wall-mounted)	1"BSP(F)	1"BSP(F)		
Air Consumption upon air motor size (see catalog)	•			
Stroke	120 (4.72)	mm (inch)		

Performance

M1 Power distributor: Wide passageway for maximum airflow

L1 Upper Body: The upper part of the pump is of robust construction and must be able to withstand the maximum pressures.

L2 Upper Valve: This valve allows material to pass from the lower chamber to the upper chamber of the pump. It is designed to limit pressure loss.

L3 Lower Valve: This valve is essential for the suction of the product. It is designed to be as wide as possible for easy filling.

Productivity

M2 The Cover: Very easy to remove and to access the repair parts

M3 The Pulse Output: The motor can be easily monitored thanks to an air pulse occurring at each reversal.

L4 Motor adaptation flange: Unique and robust assembly of the motor shaft connection to the pump shaft. Allows quick adaptation to different air motors to vary the pressure ratio of the pump.

L5 Guard: To guarantee the safety of the operators, this guard prevents contact with the moving shaft of the pump.

L6 Lower Body: The pump lower is adapted as needed to be fixed on a follower plate, immersed in a bung drum, or simply threaded for connection to a manifold.

Sustainability

M4 Brass guiding ring: Enduring and accurate guidance system

M5 Camshaft inversion system: Very reliable reversal system

L7 Upper seals packing: Our pump range has a wide range of seal materials to suit all your needs.

L8 Rod and Cylinder: The piston shaft and the cylinder are made of triple chrome steel to ensure excellent abrasion resistance.



Technologies







Triple Chrome Layer



Description



